

# Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 4-pos., M8, rear/screw mounting with M10 thread, with 0.5 m TPE litz wire, 4 x 0.25 mm<sup>2</sup>



## Key commercial data

Packing unit	1 pc
GTIN	 4 046356 605892
Weight per Piece (excluding packing)	12.85 g
Custom tariff number	85366990
Country of origin	Germany

## Technical data

### Dimensions

Length of cable	0.5 m
-----------------	-------

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Socket)
Degree of protection	IP67

### General

Rated current at 40°C	4 A
Rated voltage	30 V
Number of positions	4
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Individual wires

# Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093

## Technical data

### General

Mounting type	Rear mounting M10
---------------	-------------------

### Material

Inflammability class according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR / PA66
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	Viton

### Cable

Cable type	TPE litz wire
AWG signal line	24
Wire colors	brown, white, blue, black
Conductor material	Tin-plated Cu litz wires
Ambient temperature (operation)	-25 °C ... 90 °C (cable, fixed installation)

## Classifications

### eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

### ETIM

ETIM 4.0	EC002061
ETIM 5.0	EC002061

### UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

## Approvals

### Approvals

# Flush-type connector - SACC-DSI-M8FS-4CON-M10/0,5 - 1456093

## Approvals

Approvals

GOST

---

Ex Approvals

---

Approvals submitted


---

## Approval details




## Drawings

Dimensioned drawing




Mounting panel with feed-through hole

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

Dimensioned drawing



M8 flush-type socket