



Product Number: 8204

3M™ FC/PC SM 127um White Boot Epoxy Connector



The FC/PC Connector is a field mountable, pull-proof connector that is fully compatible with all FC connectors adhering to the NTT specification.

Additional Information:

The FC/PC connector maximizes termination yield through ease of mounting and a high performance polishing procedure. The three-piece connector design (connector, crimp ring, and boot) is mounted using the same simple process used for other 3M connectors. The FC/PC connector is available in single-mode and multimode utilizing epoxy adhesive. It is also available in multimode preloaded with 3M's Hot Melt adhesive, enabling a field termination in less than two minutes for multiple terminations. FC/PC connectors are designed for advanced fiber optic systems requiring exceptional stability and low reflections. The FC/PC hot melt multimode connector is specifically intended for ease of termination in environmentally controlled applications.

3M Id : 80-6107-6538-2

Characteristics:

| | |
|------------------------------------|--------------------------|
| Boot Color | White |
| Boot Material | Polyester |
| China RoHS - Below MCV | Yes |
| Connector Style | Field Polish / Epoxy |
| Connector Type | FC / Simplex |
| EU RoHS Compliant | Yes |
| Fiber Construction | Singlemode / 9um |
| Flame Retardant | UL-94 V-O |
| Operating Temperature Range | -40 to 85 Degree Celsius |
| Storage Temperature | -40 to 85 Degree Celsius |