

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

LOC

DIST

GP

00

REV

LTR

DESCRIPTION

DATE

DWN

APVD

C1

REVISED

PER

ECO-11-004835

11MAR11

RK

HMR

A MAX

14.73 [.580] MAX

6.40 [.252] MAX

NOTES: UNLESS OTHERWISE SPECIFIED.

1

MATERIAL: GLASS REINFORCED THERMOPLASTIC RATED 94V-0.

COLOR: BLUE.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

S. SWAN

17FEB78

CHK

APVD

NAME

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0. PLC ± -

1. PLC ± -

2. PLC ± .01

3. PLC ± .005

4. PLC ± -

ANGLES

FINISH

MATERIAL

1

PRODUCT SPEC

APPLICATION SPEC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

A1

00779

2-1437020-1

CUSTOMER DRAWING

SCALE

10:1

SHEET

1

OF

1

REV

C1

TE Connectivity

STANDARD STRAIN RELIEF, FEMALE SOCKET CONNECTOR

TE CONNECTIVITY

PART NUMBER

67.87 [2.672]	50	609-5031	7-1437021-9
55.17 [2.172]	40	609-4031	5-1437021-3
47.55 [1.872]	34	609-3431	3-1437021-0
37.39 [1.472]	26	609-2631	1-1437021-0
34.85 [1.372]	24	609-2431	9-1437020-4
29.77 [1.172]	20	609-2031	8-1437020-4
24.69 [0.972]	16	609-1631	6-1437020-4
22.15 [0.872]	14	609-1431	4-1437020-9
17.07 [0.672]	10	609-1031	3-1437020-5
11.99 [0.472]	6	609-0631	2-1437020-1
A	NO OF POSN	T&B (REF. ONLY)	TE CONNECTIVITY
PART NUMBER			

4805 (3/11)