

Datasheet

## RS Pro 50 $\Omega$ Cable Mount SMP Connector jack, Solder Termination Coaxial (RG405) Gold

RS Stock No: 878-2416



### Product Details

RS Pro cable mount SMP connector jack is designed for 50  $\Omega$  impedance applications. This connector features a gold plated beryllium copper body, solder terminal and mechanical interface according to MIL-STD-348A. It is suitable for use with RG 405 coaxial cable.

### Features and Benefits

- Nominal impedance 50  $\Omega$
- Gold plated
- Suitable for use with RG405 cable

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Cable Type	Coaxial (RG405)
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Female
Impedance	50 $\Omega$
Mating Type	Snap-On
Mounting Type	Cable Mount
Operating Frequency	18 GHz
Size	Standard
Termination Method	Solder
Operating Temperature Range	-65 to +165°C