

VIP-2/SC/FLK10

Order No.: 2315010

The illustration shows a 16-position version

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2315010>

VARIOFACE module, with screw connection and flat-ribbon cable plug connector, for mounting on NS 32 or NS 35/7.5, with pin strip and short and long locking latches for socket strips, 10-pos.



Commercial data

EAN	4046356310062
Pack	1 pcs.
Customs tariff	85369010
Weight/Piece	0.0872 KG
Catalog page information	Page 278 (IF-2009)

Product notes

WEEE/RoHS-compliant since:
09/02/2008



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Nominal voltage U_N	60 V AC/DC
Max. current carrying capacity per branch	1 A
Number of positions	10
Width	34.7 mm

Height	56 mm
Depth	65.5 mm
Status display	No
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Mounting position	Any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data

Type of connection	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M 3
Connection 2	Flat-ribbon cable connection
Type of connection	Flat-ribbon cable plug connector in acc. with IEC 60603-13
Number of positions	10

Certificates / Approvals



Certification CUL, UL

CUL

Nominal voltage U_N	125 V
Nominal current I_N	1 A
AWG/kcmil	30-12

UL

Nominal voltage U_N	125 V
Nominal current I_N	1 A
AWG/kcmil	30-12

Accessories

Item	Designation	Description
Cable/conductor		
2299204	FLK 10/EZ-DR/ 50/KONFEK	Round cable set, with two 10-pos. socket strips, (1:1 connection), cable length: 0.5 m
2299217	FLK 10/EZ-DR/ 100/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 1 m
2299220	FLK 10/EZ-DR/ 150/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 1.5 m
2299233	FLK 10/EZ-DR/ 200/KONFEK	Round cable set, with two 10-pos. socket strips, (1:1 connection), cable length: 2 m
2299246	FLK 10/EZ-DR/ 300/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 3 m
2299259	FLK 10/EZ-DR/ 400/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 4 m
2299262	FLK 10/EZ-DR/ 600/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 6 m
2299275	FLK 10/EZ-DR/ 800/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 8 m
2299288	FLK 10/EZ-DR/1000/KONFEK	Round cable set, with two 10-pos. socket strips (1:1 connection), cable length: 10 m
2295059	FLK EZ-DR.../.../...	Round cable, with preassembly, not shielded, variable cable length
2318376	VIP-CAB-FLK10-0,14/...	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: Variable
2318305	VIP-CAB-FLK10/0,14/0,5M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 0.5 m
2318318	VIP-CAB-FLK10/0,14/1,0M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 1 m
2318321	VIP-CAB-FLK10/0,14/1,5M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 1.5 m

2318334	VIP-CAB-FLK10/0,14/2,0M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 2 m
2318347	VIP-CAB-FLK10/0,14/3,0M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 3 m
2318350	VIP-CAB-FLK10/0,14/4,0M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 4 m
2318363	VIP-CAB-FLK10/0,14/6,0M	Assembled round cable with two molded 10-pos. socket strips (1:1 connection). The cable has a 90° punched on connector and a 180° punched on connector, cable length: 6 m

General


5147777	BLUEMARK X1	Printers with UV technology for printing plastic labels in UniCard format.
---------	-------------	--

Marking

0818085	UC-TM 6	UniCard sheets, for labeling terminal blocks using Zack marker strip groove,80-section, labeling with BLUEMARK X1 and CMS-P1-PLOTTER, color: White
0811862	ZB 22:UNBEDRUCKT	Zack marker strip, unprinted: 4-section, for individual labeling with M-PEN, ZB-T or CMS system, sufficient for 100 terminal blocks, for a terminal width of 22 mm, color: White
0809793	ZB 5,08:UNBEDRUCKT	Zack strip, unprinted: 10-section, for individual labeling with M-PEN, ZB-T or CMS system, sufficient for 100 terminal blocks per pack

Drawings

Circuit diagram



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford Shropshire TF7 4PG,GB
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



© 2009 Phoenix Contact
Technical modifications reserved;