



ENGLISH

# Datasheet

## Nitrile Rubber O-Ring Cord, 2.62mm Diameter, 8.5m Long

RS Stock number 683-0769



### Description:

#### Nitrile O-Ring Cord

Replacement Nitrile® O-Ring cord for fast, on the spot production of O-Rings. Available in diameters between 1.6mm and 8.4mm.

Nitrile is suitable for use within applications running at a maximum continuous temperature of 120°C (or up to 150°C intermittently). Use below -30°C requires special consideration.

### Specifications

Diameter:	2.62mm
Length:	8.5m
Material:	Nitrile Rubber