

Housing - HC-D 15-TFL-53/O1PG16G - 1672741


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for single locking latch, height 53 mm, without screw connection, 1x Pg16, straight cable entry



Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 145286
Weight per Piece (excluding packing)	94.4 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	53 mm
Width	36 mm
Length	63 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D15, A10
Type	D15
Housing type	Sleeve housing
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	Straight
Screw connection	none
Type of the screw connection	1x Pg16

Housing - HC-D 15-TFL-53/O1PG16G - 1672741

Technical data

General

Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / GL

Ex Approvals

Approvals submitted

Housing - HC-D 15-TFL-53/O1PG16G - 1672741

Approvals

Approval details

EAC

GL

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG16-S68N-PNES-GY - 1411144



Cable gland, Cable gland material: Polyamide, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16, Color: silver grey

Cable gland - G-INS-PG16-S68N-NNES-S - 1411174



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16, Color: silver

Cable gland - G-INSEC-PG16-S68N-NNES-S - 1411199



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: Yes, Connecting thread: Pg16, Color: silver

Plug for cable screw gland

Filler plugs - HC-BS-PG16 - 1674516



Filler plugs, for Pg screw connections, type Pg16

