

Datasheet

Switchgear Cable

8114630
359217
359223
359194
8114633



Image representative of range

Conductor: 7/1.04mm Plain Annealed Copper (Class 2 to IEC 60228)

Insulation: PVC (Type TI1 to BS EN 50363)

Insulation Radial Thickness: 0.80mm

Diameter Over Insulation: 5.40mm (Maximum)

Voltage Rating: 600/1000V

Conductor Resistance: 3.08 Ω /km @ 20°C (Nominal)

Cable Weight: 70.30 kg/km (Nominal)

Standard: BS 6231:2006