

Series D-A Series (revised on 8 April 2002)

Package Includes: Display Sign
I/R Remote
Power Supply Unit
Multi Lingual Instruction Manual
Mounting Brackets x 2
Side Screws x 2

Packed In Gift Box
Approval Latest CE Conformance

RAM Size 32K Max 10000 Characters

Model	Character Height mm	Display Colours	No. of Characters	Display Area mm	Case Dimensions mm	Power Rating	Weight of Unit	Weight of Package	Brightness mcd E/G	LED Dimension mm	LED Spacing mm
D-A314	51	Red	14	53 x 610	108 x 700 x 45	18VA	1.7kg	4.8kg	4.5	5	7.62
D-A320	51	Red	20	53 x 914	108 x 1005 x 45	36VA	2kg	5.2kg	4.5	5	7.62
D-A514	51	16	14	53 x 610	108 x 700 x 45	18VA	1.7kg	4.8kg	4.5/4.0	5	7.62
D-A520	51	16	20	53 x 914	108 x 1005 x 45	36VA	2kg	5.2kg	4.5/4.0	5	7.62
DX-314	102	Red	14	107 x 1220	220 x 1288 x 50	36VA	7kg	13kg	9	10	15.24
DX-514	102	16	14	107 x 1220	220 x 1288 x 50	36VA	7kg	13kg	9.0/8.0	10	15.24
SDX-314	102	Red	14	107 x 1220	220 x 1288 x 50	36VA	7kg	13kg	640	10	15.24
SDX-514	102	16	14	107 x 1220	220 x 1288 x 50	36VA	7kg	13kg	200/200	10	15.24
SD-2014	51	Red	14	53 x 610	108 x 700 x 45	36VA	1.7kg	5.2kg	1000	5	7.62
SD-3014	76	Red	14	80 x 912	134 x 965 x 76	36VA	2.2kg	5.5kg	1000	5	7.62
DS 310	30	Red	10	32 x 275	80 x 340 x 44	18VA	0.7Kg	1.9Kg	4.5	3	4.57
DS 514	30	13	14	32 x 366	80 x 431 x 44	18VA	1Kg	2Kg	4.5/4.0	3	4.57
DS 520	30	16	20	32 x 549	80 x 614 x 44	36VA	1.4Kg	2.4Kg	4.5/4.0	3	4.57