

Datasheet

RS Pro 50 W Electronic Lighting Ballast, 220 to 240 V

RS Stock No: **796-1905**



Product Details

RS Pro 50 W electronic lighting ballast works with voltages ranging from 220 - 240 V. This dimmable electronic driver can power both voltage LED strips and power current LEDs. It delivers high power, with active PFC and flexible selection of the output current.

Features and Benefits

- Multi-power driver supplied with dip-switch for the selection of the output current
- Active power factor corrector
- Protections against overheating, short circuits, mains voltage spikes and overloads
- Can be switched on and off on secondary circuit for power LED

**Specifications:**

Ballast Type	Electronic
Dimensions	124 x 79 x 22 mm
Dimmable	Yes
Dimming Protocol	DALI
Frequency	50 to 60 Hz
Height	22 mm
Length	124 mm
Standards Met	EN 50172 (VDE 0108); EN 55015; EN 61000-3-2; EN 61000-3-3; EN 61347-1; EN 61347-2-13; EN 61547; EN 62384
Voltage Rating	220 to 240 V
Wattage	50 W
Width	79 mm