


**HC-B 16-TFL-60/O1M25S**

Order No.: 1604796



HEAVYCON sleeve housing B16, with single locking latch, height 60 mm, with support M25, lateral conductor exit

Commercial data	
GTIN (EAN)	 4 017918 882747
sales group	D002
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 571 (PC-2011)

## Product notes

WEEE/RoHS-compliant since:  
01/31/2006



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
<b>General data</b>	
Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Design	B16
Height	60 mm
Width	43 mm

Length	94 mm
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Lateral
Pg screw connection	None
Type of the screw connection	1x M25
Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray

### Certificates / Approvals



Certification

GOST

### Diagrams/Drawings

Dimensioned drawing

