

Product information UL12500



Informations

Short description:	Integral socket USA/Canada, 15A, 125V, black
Description:	Integral socket for USA in accordance with UL 498 / NEMA 5-15 R and for Canada in accordance with CSA C22.2 no.: 42, 1-pole + N + earth, 15A, 125V, thermoplastic, colour black, with screw terminal, quadruple flange fastening and cover flap, cable connection
Product number:	UL12500

Attributes of ETIM

Mounting method	Other
Colour	Black
Model	American National Standard
Cover	Complete housing
Connection type	Screwed terminal
Surface treatment	Other
Material quality	PVC
Special power supply	No special power supply
Material	Plastic
Type of fastening	Mounting with screw
Imprint/indication	Without imprint
Type of surface	Matt
Number of units	1
With hinged lid	Yes

With child-protection	No
Label space/information surface	No
RAL-number (akin)	9005
Lockable	No
Eject-mechanism	No
With lighting	No
Over voltage protection	No
Fault current protection	No
With miniature fuse	No
Halogen free	Yes
Switch-off function	No
Rotated central insert	No
Nominal current	15
Nominal voltage	125
Rated fault current	-
For heavy conditions (in accordance with VDE)	No
Frequency	60
Suitable for degree of protection (IP)	IP44