

Terminals

KLS 25



- Rated connecting capacity: 6-35 mm², Cu

- for insertion in cable junction boxes
- current carrying capacity: 102 A
- 5-pole per pole 6 x 6 mm² sol, 6 x 10 mm² sol/ f*, 4 x 16 mm² s/ f*, 4 x 25 mm² s/ f*, 2 x 35 mm² s/ f* f* = with gas-tight end ferrule
- for cable junction boxes K 8250, K 8500, K 9250, K 9500, KF 4250, KF 5250, KF 5500, KF 8250, KF 8500, KF 9250, KF 9500, KD 4250, KD 5250
- complete with fixing elements

rated insulation voltage	Ui = 690 V a.c./d.c.
Dismantling length	16 mm
tightening torque for terminal	3,0 Nm
Weight	0,3 kg

Drawings

Dimension drawing

