

# Adapter - HC-NPT-1 1/4-M40 - 1687587

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M40 to 1 1/4"



The illustration shows version HC-NPT-1/2-M20



## Key commercial data

Packing unit	10 pc
GTIN	 4 017918 822736
Weight per Piece (excluding packing)	89.96 g
Custom tariff number	74199990
Country of origin	Germany

## Technical data

### Ambient conditions

Degree of protection	IP68 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

### General

Material	Nickel-plated brass
Material, O-ring	NBR
Thread type on connection side	M40

## Classifications

### eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109

# Adapter - HC-NPT-1 1/4-M40 - 1687587

## Classifications

### eCl@ss

eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

### ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

---

### Approval details

GOST 
--

## Drawings

## Adapter - HC-NPT-1 1/4-M40 - 1687587

Dimensioned drawing

