

## Power module - EMD-SL-PS45-500AC - 2885317

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Power modules, pluggable, for EMD-FL-..., supply voltage: 425...550 V AC



### Why buy this product

- ✓ Monitoring range up to 7.2 kW
- ✓ Temperature monitoring of the motor winding
- ✓ Variable supply voltage range
- ✓ Separately adjustable startup and response delays
- ✓ Detection of switched off loads

### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 996550
Weight per Piece (excluding packing)	94.2 g
Custom tariff number	85043180
Country of origin	Germany

### Technical data

#### Dimensions

Width	32 mm
Height	35 mm
Depth	26 mm

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

#### Input data

Nominal input voltage	500 V AC (50/60 Hz)
-----------------------	---------------------

## Power module - EMD-SL-PS45-500AC - 2885317

### Classifications

#### eCl@ss

eCl@ss 4.0	27371105
eCl@ss 4.1	27371105
eCl@ss 5.0	27049090
eCl@ss 5.1	27049201
eCl@ss 6.0	27049201
eCl@ss 7.0	27049201
eCl@ss 8.0	27049201

#### ETIM

ETIM 2.0	EC001438
ETIM 3.0	EC001438
ETIM 4.0	EC001438
ETIM 5.0	EC002540

#### UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121535