

19


RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

© COPYRIGHT 19

LOC	DIST	REVISIONS					
J	---	P	LTR	DESCRIPTION	ECN	DATE	DWN
			C	REVISED	J-9884	8.MAY'87	Y.F
			D	REDRAWN WITH CHANGE	FJ00 - 1547 - 98	7.AUG'98	M.C



注;
1. 適用ハウジング型番 172076

NOTE;
1. APPLICABLE HOUSING P/N:172076

170333-1	PRE TINNED BRASS 鍍めつき付真鋼0.4t	170327-1
LOOSE PIECE P/N ばら状端子型番	MATERIAL 材料	P/N 型番
WIRE RANGE 総合電線断面積(AWG#22-#18)	INSULATION DIA 被覆外径	
0.31~0.89mm ²	1.5~3.1mm	
MATERIAL 材料	SEE TABLE 表参照	FINISH 仕上
AMP 日本エー・エム・ピー株式会社 Kawasaki, Japan		
NAME 名称 "250" SERIES POSITIVE LOCK (MARK II) REC. "250"シリーズポジティブロック(マークII)リセブタクル		
SIZE A4	CAGE CODE 00779	DRAWING NO C=170327
RESTRICTED TO -		
SCALE 尺度 4-1		SHEET 1 OF 1
REV D		

DIMENSIONS: 単位 概 mm	DWN Dwn. Sugawara CHK M.C.
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M.C.
一般公差	PRODUCT SPEC 製品規格
10% : ±0.2	108-5127
30% : ±0.25	APPLICATION SPEC 取付適用規格
50% : ±0.3	114-5042
ANGLE : ±0.3°	WEIGHT ---