

Datasheet

RS Pro Straight 50Ω Cable Mount BNC Connector, jack, Clamp Termination RG58A

RS Stock No: **546-4415**



Product Details

RS Pro cable mount BNC connector has a nickel plated body, gold plated centre contact and is suitable for RG58A cables. This 50 Ω straight BNC connector comes with cable jack, clamp termination.

Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Jack, clamp termination

**Specifications:**

Body Orientation	Straight
Body Plating	Silver
Cable Type	RG58A
Contact Material	Copper
Contact Plating	Silver
Gender	Female
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Clamp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-65 to +165°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)