

Artikelbezeichnung <i>Article description</i>	arktis-weiß <i>arctic white</i>			palisander braun <i>rosewood brown</i>		
	Art.-Nr <i>Art.No.</i>	EAN-Code <i>EAN code</i>	BE <i>PUC</i>	Art.-Nr <i>Art.No.</i>	EAN-Code <i>EAN code</i>	BE <i>PUC</i>
 <p>Aus- und Wechselschalter <i>off and change-over switch</i></p> <p>PROFI-PACK: 4 Aus- und Wechselschalter <i>PROFI-PACK: 4 Universal switches . (off and change-over)</i></p> <p>Universalschalter (A/W)beleuchtbar <i>Universal switch (off and change-over) illuminable</i></p>	6506.0208.9	4008224454636	10	6506.2608.7	4008224454643	10
	6506.0212.0	4008224476720	10	6506.2612.8	4008224476737	10
	6506.0213.7	4008224500418	10			
	6526.0201.2	4008224454650	1	6526.2601.0	4008224454667	1
6506.9308.3	4008224454674	3	6506.7608.2	4008224454681	3	
 <p>Kreuzschalter <i>Cross switch</i></p> <p>Taster neutral <i>Pushbutton switch</i></p> <p>Taster beleuchtbar <i>Pushbutton, illuminable</i></p>	6507.0208.2	4008224454698	3	6507.2608.0	4008224454704	3
	6507.0212.3	4008224476768	3	6507.2612.1	4008224476775	3
	6507.0213.0	4008224500432	3			
	6513.0208.1	4008224454711	5	6513.2608.9	4008224454728	5
	6513.0212.2	4008224476782	5	6513.2612.0	4008224476799	5
	6513.0213.9	4008224500449	5			
	6513.9308.5	4008224454735	3	6513.7608.4	4008224454742	3
 <p>Kontrollschalter (A/W) mit Linse und eingesetzter Glühlampe <i>Control switch, illuminated flush, on/off and change over switch</i></p>	6516.9308.4	4008224454759	3	6516.7608.3	4008224454766	3
	6516.9312.5	4008224476829	3	6516.7612.4	4008224476836	3
	6516.9313.8	4008224500456	3			
 <p>Wechsel/Wechselschalter <i>double change-over switch</i></p> <p>Serienschalter <i>Series switch</i></p> <p>Jalousieschalter <i>Venetian switch</i></p>	6503.0208.0	4008224454773	3	6503.2608.8	4008224454780	3
	6503.0212.1	4008224476843	3			
	6505.0208.6	4008224454797	5	6505.2608.4	4008224454803	5
	6505.0212.7	4008224476867	5	6505.2612.5	4008224476874	5
6505.0213.4	4008224500470	5				
65150208.7	4008224454810	3	6515.2608.5	4008224454827	3	
65150212.8	4008224476881	3	6515.0213.5	4008224500487	3	
 <p>Elektronischer Dimmer mit Wippen-Wechselschalter nur für konventionelle Trafos. <i>Electronic dimmer With rocker universal switch only for conventional transformer.</i></p> <p>Elektronischer Dimmer mit Wippen-Wechselschalter für dimmbare elektronische Trafos. <i>Electronic dimmer with rocker universal switch for dimmable electronic transformer.</i></p>	8034.0208.7	4008224454834	2	8034.2608.5	4008224454841	2
	8034.0212.8	4008224476898	2	8034.2612.6	4008224476904	2
	8034.0213.5	4008224500494	2			
8035.0208.0	4008224454858	2				
8035.0212.1	4008224476911	2				
8035.0213.8	4008224500500	2				
 <p>Vollelektronischer Sensor-Dimmer DIMMAT® für Glüh- und 230 V-Halogen-, sowie Nieder- volt-Halogenlampen mit konventionellen Trafos Nicht für elektronische Trafos.</p> <p><i>Fully automatic sensor dimmer DIMMAT® For light bulbs and 230 V halogen lights, as well as low voltage halogen lights, 40-400 VA, 230 V, 50 Hz. For conventional transformer.</i></p>	8036.0208.3	4008224454865	2	8036.2608.1	4008224454872	2
	8036.0212.4	4008224476928	2	8036.2612.2	4008224476935	2
	8036.0213.1	4008224500517	2			
 <p>infraCONTROL 2002 Luxus Unterputz Infrarot-Bewegungsschalter mit Umschalter: Dauer-EIN, Automatik, Dauer-AUS, 2-Draht-Gerät, Überwachungswinkel ca. 180°</p> <p><i>infraCONTROL 2002 Luxus - flush mounted, Infrared motion switch with switching: permanently ON, automatic, permanently OFF 2-wire device for resistive loads, detection angle approx. 180°</i></p>	8058.0001.0	4008224512947	1			
 <p>Raumthermostat „Öffner“ Leitungsanschluß 0,75 mm² bis 2,5 mm², Temperatur- bereich 5° C - 30° C, Nachtabsenkung 4 Kelvin, 10 (4) AX, 250 V, 2.200 W <i>Room thermostat break contact</i></p> <p>Raumthermostat „Wechsler“ Temperaturbereich 5° C - 30° C, Nachtabsenkung 4 Kelvin, 5 (2) AX, 250 V, 1.100 W <i>Room thermostat change-over contact,</i></p>	2901.0201.1	4008224472951	1			
	2904.0201.0	4008224510264	1			
 <p>Elektronische Zeitschaltuhr, 6 A, 250 V, 1.500 W/VA, 10 Programme, Zufallsgenerator, Count-Down-Funktion, LCD-Display, Gangreserve ca. 100 Stunden,</p> <p><i>Electronic timer 6 A, 250 V, 1.500 W/VA, 10 programs, random switch, count-down function, LCD Display, backup time approx. 100 hours</i></p>	2902.0201.4	4008224472968	1			
 <p>Rolladenzeitschaltuhr, kombinierbar mit den Schalterpro- grammen Paris, Malibu, Denver und Vision zur automa- tischen Steuerung von Rollläden und Markisen, Ferien- und Handsteuerung, LCD-Display, Gangreserve (min. 18h), je 7 Auf- und Abzeiten einstellbar, 6 AX, 250 V, 1.500 W/VA <i>Timer for the automatic control of motor driven shutters and sun blinds, can be combined with Paris, Malibu, Denver and Vision, holiday- and manual control, LCD-Display, back-up time (max. 18h), 7 up- and down-times programmable</i></p> <p>Sonnensensor für Rolladenzeitschaltuhr <i>Sensor for shutting-timer</i></p>	1985.1301.6	40082224406000	1			
	1986.0001.9	4008224414685	1			