

LOC	DIST	REVISIONS					
E	B	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-07-011423	14/05/07	AM	FWK

NOTES:

1. ELECTRICAL DATA:

CONTACT RESISTANCE: 10 mOhm MAX

INSULATION RESISTANCE: 100 MOhm MIN at 500VDC

CURRENT RATING: 5 AMPS

BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
2. ENVIRONMENTAL:

OPERATING TEMPERATURE: -20°C TO +80°C


SEALING REQUIREMENTS: IP67
3. PROD SPEC:

108-3641
4. PACKAGING:


107-3334
5. FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
6. ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	PIN CONTACT	BRASS	0.15µm GOLD PLATED OVER NICKEL	4
4	4 CORE CABLE (CORES 22AWG TO UL2464)	PVC JACKET UV RESISTANT	BLACK	1

PIN ASSIGNMENTS
FRONT VIEW




4	BLACK
3	BLUE
2	WHITE
1	BROWN
PIN	WIRE COLOUR



10000	500 mm	M12 RIGHT ANGLED MALE CONNECTOR 10.0m CABLE	1838250-5
7000	350 mm	M12 RIGHT ANGLED MALE CONNECTOR 7.0m CABLE	1838250-4
5000	250 mm	M12 RIGHT ANGLED MALE CONNECTOR 5.0m CABLE	1838250-3
3000	150 mm	M12 RIGHT ANGLED MALE CONNECTOR 3.0m CABLE	1838250-2
2000	100 mm	M12 RIGHT ANGLED MALE CONNECTOR 2.0m CABLE	1838250-1
DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

-

DWN
H M RAGHAVENDRA

CHK
F.WHEELER-KING

APVD
F.WHEELER-KING

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

22AUG05

15DEC05

15DEC05

tyco
Electronics

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

M12 RIGHT ANGLED MALE CONNECTOR
4 POSITION, PVC CABLE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1838250	-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
B