






LOC	DIST	REVISIONS					
FT	64	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M	REV PER OG3C-0214-99	24AUG00	BH	HW
			M1	REVISED PER ECO-10-000443	15JAN10	KK	AEG




SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -6,-7 & -8 ONLY



1. RECEPTACLE ACCEPTS AN .008-.014 THK. I.C. LEAD.
2. TWO .000030 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -1,-2 & -3 ONLY



		TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-8	
	4	OBSOLETE	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-7	
	4	OBSOLETE	TINNED	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-6	
SUPSD BY	643640-2	4	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-4	
		4	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-3
		4	OBSOLETE	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-2
			TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643640-1
CONTACT FINISH			CONTACT MAT'L	HOUSING MATERIAL	PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN M.CYRUS CHK N.JONES APVD J.GRAY	6-14-84 7-3-84 7-10-84	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC	± -	SOCKET ASSY, SIP, 8 POS, DIPLOMATE DL -		
		1 PLC	± -			
		2 PLC	± -			
		3 PLC	± .005			
		4 PLC	± -			
MATERIAL		FINISH	WEIGHT	SIZE		
SEE TABLE		SEE TABLE	-	A1 00779 643640		
CUSTOMER DRAWING				SCALE 5:1 SHEET 1 OF 1 REV M		