


Passeinsatz für Einsätze E14 4 A Combi Check 2MM

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Type	Combi Check 2MM
Order No.	9204230000
Version	2-pole voltage tester type 1156, Yes - visual + acoustic
GTIN (EAN)	4032248616497
Qty.	1 pc(s).

Data sheet

**Passeinsatz für Einsätze E14 4 A
Combi Check 2MM**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	290 g	Net weight	357 g
--------	-------	------------	-------

Product data

Rated voltage, min.	6 V	AC voltage measuring range	6-690 V
Frequency range, min.	0 Hz	Frequency range, max.	100 Hz
Rated voltage, max.	690 V AC/DC	Protection degree	IP 65
Battery type	1.5 V type AAA battery	Peak voltage resistance	8 kV
Display	LED	DC voltage display	6,12, 24, 50, 120, 230, 400, 690 V
AC voltage display	6,12, 24, 50, 120, 230, 400, 690 V		

Classifications

eClass 6.2	27-20-03-08
------------	-------------

Product information

Descriptive text technical data	Buzzer included
---------------------------------	-----------------

Approvals

ROHS	Conform
------	---------