



ENGLISH

Datasheet

## RS Pro Stem Castor, 160kg, Nylon tyres

RS Stock No: **420-9009**



### Product Details

RS Pro stem swivel castor features nylon tyre for non-marking floor surface and has load capacity of 160 kg. Jacking castor provides quick and accurate vertical adjustment when fitted to platforms, staging, cabinets, assembly jigs and tool transfer units, etc.

### Features and Benefits

- 360° rotation with 75 mm lift
- Plain wheel bearings
- Plate fitting
- Provide a high degree of manoeuvrability in transporting plant and equipment

**Specifications:**

Features	Jacking
Hub Bearing Type	Plain Bore
Hub Material	Nylon
Includes Brake	No
Load Capacity	160 kg
Mounting Type	Threaded Stem
Overall Height	444 mm
Rotation	Swivel
Stem Diameter	10.5 mm
Tyre Material	Nylon
Weight Class	Light Duty
Wheel Diameter	100 mm
Wheel Width	35 mm