

Conductor marker - UC-WMC 4,4 (15X5,5) - 0818182

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Conductor marker, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Clip on, Cable diameter: 2.8-4.4 mm, Lettering field: 15 mm x 5.5 mm



Why buy this product

- ✓ The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 133517
Weight per Piece (excluding packing)	11.16 g
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Width (a)	15 mm
-----------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	15
Number of individual labels per row	3
Printability	Inkjet printing
	Plotter
Device	5147888 BLUEMARK LED

Conductor marker - UC-WMC 4,4 (15X5,5) - 0818182

Technical data

General

	5147999 BLUEMARK CLED
	5144615 CMS-P1-PLOTTER
	5146082 P1 UC-MAG 2
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Conductor marker - UC-WMC 4,4 (15X5,5) - 0818182

Accessories

Accessories

Magazine

Magazine - P1 UC-MAG 2 - 5146082



Magazine, for CMS-P1-PLOTTER, for accommodating UC-WMC 4.4...

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>