

General Information

Extended Product Type:	232-C6
Product ID:	2CMA193528R1000
EAN:	7392696935289
Catalog Description:	Connector, 6h, 32A, IP44, 2P+E
Long Description:	Connector, earthing sleeve position 6h, rated current 32A, IP44 splashproof, 2-poles+earth, 50 - 60 Hertz, color code blue

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Connectors

Ordering

EAN:	7392696935289
Minimum Order Quantity:	10 piece
Country of Origin:	Czech Republic (CZ)

Dimensions

Product Net Width:	96 mm
Product Net Height:	96 mm
Product Net Length:	177 mm
Product Net Depth:	96 mm
Product Net Weight:	0.258 kg

Container Information

Package Level 1 Width:	180 mm
Package Level 1 Length:	155 mm
Package Level 1 Height:	378 mm
Package Level 1 Gross Weight:	0.258 kg
Package Level 1 EAN:	7392696935289
Package Level 1 Units:	10 piece

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
--------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CMC700005D0001
Environmental Information:	2CMC700001D0002
RoHS Information:	2CMC700057D0001

Additional Information

Additional Information:	Cable entry, compression gland
Cable Cross-Section:	2.5 ... 6 mm ²
Color:	Blue
Degree of Protection:	IP44
Enclosure Material:	Polyamide
Frequency (f):	50 Hz
Function:	Connector
IIT Publishing Status:	Level 0 - Information enabled
Invoice Description:	Ind. P&S#232-C6
Number of Poles:	3
Object Classification Code:	2CMT005069
Product Main Type:	C
Product Name:	Industrial Connector
Protection Type:	Splashproof
Rated Current (I _n):	32 A
Rated Voltage (U _r):	200 ... 250 V
RoHS Date:	L23
Standards:	IEC 60309-1,-2
Suitable For:	Connectors
Suitable for Product Class:	Industrial Plugs and Sockets

Classifications

E-nummer:	2416185
UNSPSC:	39120000

