

D-SUB pressure nut - VS-PG11 (3- 7) - 1688117


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



D-SUB cap nut with line seal, for conductor diameter of 3 mm ... 7 mm, for sleeve housing VS-15-...



Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 182274
Weight per Piece (excluding packing)	4.48 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

External cable diameter	3 mm ... 7 mm
-------------------------	---------------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

General

Color	gray
Type of the screw connection	Pg11
Housing material	PA
Seal material	Neoprene
Inflammability class according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701

D-SUB pressure nut - VS-PG11 (3- 7) - 1688117

Classifications

eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261203
eCl@ss 7.0	27440290
eCl@ss 8.0	27440290

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC002355

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing

D-SUB cap nut