

Datasheet

## RS Pro Straight 50Ω Coaxial Adapter BNC Socket to TNC 0 to 4GHz

RS Stock No: **793-3607**



### Product Details

RS Pro straight BNC Socket to TNC coaxial adapter comes with waterproof IP68 inner sealing against gas and moisture ingress between insulators, inner and outer conductors and connector body and panel sealing between the connector body and panel mounting hole. This waterproof RF coaxial BNC jack to TNC jack adapter has a nickel plated brass body, PTFE insulator, silicone gasket and a gold plated centre contact.

### Features and Benefits

- BNC Socket to TNC coaxial adapter
- Nickel plated brass body, PTFE insulator, silicone gasket and a gold plated centre contact
- 50Ω impedance

**Specifications:**

Adapter Type A	BNC
Adapter Type B	TNC
Adapter Type	BNC Socket to TNC Socket
Body Orientation	Straight
Body Plating	Nickel
Contact Material	Brass
Contact Plating	Gold
Gender A	Socket
Gender B	Socket
Impedance	50 $\Omega$
Length	39.5 $\pm$ 0.3 mm
Operating Frequency	0 to 4 GHz
Body Material	Brass
Insulation Material	PTFE
Operating Temperature	-65 to +165°C
Voltage Rating	500 V