





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A3	REVISED PER ECO-11-004820	11MAR2011	RK	HMR





- 1 BRASS, 0.20 THK. REF
- 2 NICKEL UNDERPLATE OVER ALL
- 3 0.00254 MIN THK BRIGHT TIN ENTIRE CONTACT OVER NICKEL UNDERPLATE
- 4 TYCO ELECTRONICS LOGO LOCATED APPROXIMATELY AS SHOWN



SECTION T-T
SCALE 20:1

SECTION Y-Y
SCALE 20:1



18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	LOOSE PIECE	2 3	2-2106124-7
18.24	2.40	2.60 2.20	1.55	1.96 1.57	1.30 - 1.60	22-24 AWG	ON REEL	2 3	2-2106124-2
18.24	3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	LOOSE PIECE	2 3	2106124-9
18.24	3.01	2.80 2.40	2.05	2.32 1.92	1.70 - 2.10	18-20 AWG	ON REEL	2 3	2106124-2
DIM E	DIM D	DIM C	DIM B	DIM A	INSULATION DIA	WIRE RANGE	REMARKS	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. BROWN 05MAR2009	TE Connectivity				
DIMENSIONS: mm			CHK A. BUCHER 05MAR2009					
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD -	NAME CONTACT, TAB, CRIMP SNAP-IN SLIM SEAL SSL				
0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±1° FINISH			PRODUCT SPEC 108-2391 APPLICATION SPEC 114-13261 WEIGHT -	SIZE A2				
MATERIAL			CUSTOMER DRAWING	CAGE CODE 00779				
SEE NOTES			SCALE 10:1	DRAWING NO 2106124				
			SHEET 1	REV A3				