


Spherical roller bearings, cylindrical and tapered bore



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN	C_0	kN	r/min	kg	-	* - SKF Explorer bearing
60	110	34	156	166	18,6	-	1,30	BS2-2212-2CS/VT143 *	



Calculation factors

- e 0,24
- Y_1 2,8
- Y_2 4,2
- Y_0 2,8