




LOC	DIST	REVISIONS						
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		D		REVISED PER ECO-09-017403	30JUL2009	ZMR	PAR	

1. MATERIAL:
HOUSING - PBT POLYESTER, COLOR: BLACK
TERMINAL - 0.36[.014] THICK PHOS BRONZE PLATED WITH 1.27µm [.000050] THICK HARD GOLD IN LOCALIZED GOLD PLATE AREA AND 2.03µm [.000080] THICK MATTE TIN IN SOLDER AREA OVER 1.27µm [.000050] THICK NICKEL UNDERPLATE
SHIELD - 0.25 [.010] THICK COPPER ALLOY PLATED WITH 3.0µm [.000120] MINIMUM THICK REFLOWED TIN
- 2 CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68, SUBPART F.
- 3 DIMENSIONS MEASURED ALONG FRONT EDGES OF MATING FACE
- 4 BULK PACKAGED IN A TRAY
- 5 32 ASSEMBLIES PACKAGED PER TUBE. SEE DETAIL B

1.78-2.79[.09±.02]	4	5555153-6
2.54-3.05[.11±.01]	4	5555153-5
3.30-4.32[.15±.02]	5	5555153-3
3.30-4.32[.15±.02]	4	5555153-1
DIM A	PACKAGED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT/L.A. MAYER CHK P. RECCE APVD S. FLICKINGER	05NOV2007 05NOV2007 05NOV2007	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		MODULAR JACK ASSEMBLY, SHIELDED, 8 POSITION, LOW PROFILE, RIGHT ANGLE, PANEL GROUND WITH PANEL STOPS	
		PRODUCT SPEC		108-1163	
	1 P L C ± - 2 P L C ± - 3 P L C ± 0.1% [0.005] 4 P L C ± - ANGLES ± -	APPLICATION SPEC		114-2048	
		WEIGHT		-	
MATERIAL	FINISH	DRAWING NO		RESTRICTED TO	
SEE NOTE 1	SEE NOTE 1	A1 00779 C=5555153		-	
CUSTOMER DRAWING		SCALE		4:1	
		SHEET		1 OF 1	
		REV		D	