

1000mm Wide x 550mm Deep x 955mm High Maintenance Trolley

- Welded steel construction
- 50 Kg U.D.L. capacity drawers with drawer interlocks to prevent accidental opening whilst in transit
- Push - pull handle
- 30mm multiplex worktop
- 125mm diameter castor set, 2 with brake
- Maximum combined load capacity 200kg
- Powdercoat RAL5010 blue / RAL7035 grey finish

Specification	Bott Ref.
1x 700mm cupboard with shelf, 4x 175mm Drawers.	16913221.11V

Robust Mobile Housing



Reinforced, welded steel housings for long service life in tough industrial environments.

50kg Drawers



Standard fitment drawers are 50kg U.D.L. capacity with roller bearing slides for ease of action even under full load.

Drawer Interlocks



Integrated into the drawer front on mobile cabinets and maintenance trolleys the interlocks prevent accidental opening whilst in transit.

Quality Castors



Rubber tyred castors and swivel and brake mechanisms feature on all mobile models with 200kg total weight capacity.

