




- 1 POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR: NATURAL
- 2 POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR: BLACK
- 3 POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4 ZINC PER QQ-Z-363.
- 5 PHOSPHOR BRONZE PER QQ-B-750.
- 6 BRASS PER ASTM-B-453.
- 7 BRASS PER ASTM-B-16.
- 8 NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 9 TIN PLATE PER ASTM-B-545. 3.81 μ m [.000150] MINIMUM THICK.
- 10 GOLD PLATE PER MIL-C-45204, 0.76 μ m [.000030] MINIMUM THICK.
- 11. SEE INSTRUCTION SHEET 408-2769.

-				-	-	B	1-329631-2	1-329632-2	5227222-6	5227222-9					
3.48 [.137]						A	-	-	-	5227222-6					
3.48 [.137]						A	-	-	-	5227222-3					
3.48 [.137]						A	-	-	-	5227222-2					
3.48 [.137]						A	-	-	-	5227222-1					
C	MOUNTING PIN PLATING	GROUND POST PLATING	CONTACT POST PLATING	CONTACT PLATING	HOUSING MATERIAL	VIEW	③ JAM NUT QTY=1	② LOCKWASHER QTY=1	① ASSEMBLY QTY=1	PART NUMBER					
THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN J. ALCORTA - 26APR2005 CHK J. HAVENER 26APR2005 APVD J. LIPPERT 26APR2005		Tyco Electronics Corporation Harrisburg, Pa 17105-3608							
						DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		JACK, VERTICAL, 50 OHM, PCB, SERIES BNC			
								0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-12078		SIZE CAGE CODE DRAWING NO RESTRICTED TO			
						APPLICATION SPEC		MATERIAL 		FINISH 		WEIGHT -		A1 00779 C=5227222	
						CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1		REV B			