

Terminal boxes KL without gland plate – KL 1519.510



Product description

Material:	• Enclosure: Sheet steel • Cover: Sheet steel, all-round foamed-in PU seal
Surface finish:	• Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint
Colour:	• RAL 7035
Protection category IP to IEC 60 529:	• IP 66
Protection category NEMA:	• NEMA 4
Supply includes:	• Enclosure with cover • Quick-release fastener including plastic bushes
Packs of:	• 1 pc(s).
EAN:	• 4028177251311
Customs tariff number:	• 94032080

Product features

Dimensions:

- Width: 600 mm
- Height: 200 mm
- Depth: 80 mm

Weight:

- 4.6 kg

Approvals

Approvals:

-  [Bureau Veritas \(EN\)](#)
-  [VDE \(EN, DE\)](#)
-  [UL \(EN\)](#)
-  [TÜV \(EN\)](#)
-  [TÜV \(DE\)](#)
-  [Russian Maritime Register of Shipping \(RU, EN\)](#)
-  [Lloyds Register of Shipping \(EN\)](#)
-  [C-UL \(EN\)](#)
-  [CSA \(EN\)](#)
-  [Germanischer Lloyd \(EN\)](#)

Declarations:

-  [Manufacturer's declaration \(EN, DE\)](#)
-  [Declaration of conformity \(EN, DE\)](#)

Downloads

Documentation:

-  [Instructions \(EN, DE\)](#)

CAD drawings:

- Request