

Datasheet

DC Axial Fan, 80 x 80 x 15mm, 51m³/h, 2.3W, 12 V dc (OD8015 Series)

RS Stock No: 541-5025

Product Details



RS Brushless High Performance Ball Bearing Fan

RS brushless high performing ball bearing fans provide a general purpose, compact, cost-effective and reliable solution to a variety of requirements.

Black construction

Approvals

UL, cUL, TUV

DC Axial

Specification

Supply Voltage	12 V dc
Dimensions	80 x 80 x 15mm
Height	80mm
Width	80mm
Depth	15mm
AC or DC Operation	DC
Air Flow	51m ³ /h
Power Consumption	2.3W
Maximum Current	180mA
Bearing Type	Ball
Noise Level	33dB
Fan Speed	3200rpm



Specification

Configuration	Square
Static Pressure	0.11in/H2O
Termination Type	Lead Wire
Special Features	Auto Restart, Brushless DC, Locked Rotor Protected Motor, Polarity Protected
Series	OD8015