

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
This drawing is the property of Pressmaster AB. Protected in accordance with privailing law.

För icke direkt toleranssatta mått
gäller toleransklass
General tolerances if not other-
wise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2


Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
No sharp edges unless otherwise specified.

Övriga generella toleranser enligt
ritning 4100-4644.
Additional general tolerances in
accordance with drawing 4100-4644.


Packas i 10-pack låda E med etikett/kort D

Tolkmått / Gauge dimensions (mm)		
Urtag/ Nest	Gåtolk/ GO	Stopptolk/ NO GO
2,5-4	Ø 2,60	Ø 2,70
6	Ø 4,07	Ø 4,17



4101-3741

Placeras inuti vikblistret /
Placed inside the clamshell



Pressback kompl. placeras i
hållaren vid packning/

Die Compl. placed in
holder when packaging

4300-3540/AAB	4101-6640 A	4101-3490	4300-3540	-	-
4300-3540			4101-5848		
ART.NR.VAR.	A	B	C	D	E

Material			Behandling/Treatment			Status Prel.utc.	
Konstr/Design OS	Ritad/Drawn OS	Datum/Date 2010-02-10		Skala/Scale 1:1	Kontr/Checked	Godk/Approved	Anne/Blank
pressmaster ®			Benämning/Denomination PRESSBACKSET Solar MC-3			Vikt/Weight,gram	Art grp 011
			DIE SET			Ritn nr/Drawing no 43003540	REV 006