



Main

Range	TeSys
Device short name	LUA8
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	2 NO
Signalling function	Start-stop
[Ue] rated operational voltage	24...250 V AC 24...250 V DC
[Ith] conventional free air thermal current	5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.048 kg
Connections - terminals	Screw clamp terminals

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1301 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications