

# Specifications for BMP41/BMP51/BMP53 Labelmaker Labels

<b>Adhesive</b>	Permanent Acrylic
<b>Article No.</b>	131580
<b>Brady Material No.</b>	<a href="#">B-427</a>
<b>Material Type</b>	Self-laminating Vinyl
<b>Colour</b>	Black on White/Transparent
<b>Finish</b>	Matt
<b>Order Reference</b>	M-49-427
<b>Printable Area - Height (mm)</b>	9.53
<b>Printable Area - Width (mm)</b>	25.40
<b>Printer Compatibility</b>	BMP41; BMP51; BMP53
<b>Size - Height (mm)</b>	25.40
<b>Size - Width (mm)</b>	25.40
<b>Additional Information</b>	Self-laminating; Self-extinguishing; Excellent water & oil resistance; Excellent abrasion and smudge resistance
<b>Thickness (mm)</b>	0.102
<b>Total Qty per Pack</b>	260 Label(s) / Box
<b>Vertical Repeat (mm)</b>	28.58
<b>Wire Gauge</b>	12-10
<b>Approval/Compliance</b>	UL Recognised
<b>Adhesive (Y/N)</b>	Yes
<b>Application</b>	Voice & Data Communication; Wire & Cable Marking
<b>Industry</b>	Data & Telecommunications; Electrical
<b>Max. Service Temp. °C</b>	60
<b>Max. Wire/Cable Diameter (mm)</b>	5.10
<b>Min. Service Temp. °C</b>	-80

<b>Min. Wire/Cable Diameter (mm)</b>	2.70
<b>Shape</b>	Square
<b>Software</b>	LabelMark
<b>Surface</b>	For smooth & textured/rough surfaces
<b>Voice/Data Application</b>	2 Pair Fibre/Coaxial; Single/Multi-Mode