

Datasheet

Steel Zinc Plated Toggle Latch

RS Stock number [197-4110](#)



Description:

A basic compact toggle latch.
Suitable for light duty applications.
M4 fixing for catch and latch.
25kgf operating tension.
Catch to latch distance 44mm.

Specifications:

Depth:	12 mm
Finish:	Zinc Plated
Length:	50 mm
Material:	Steel
Operating Tension:	25 kgf
Width:	22.4 mm

Dimensional Drawing:

