

# PLC-BSC-230UC/21HC

Order No.: 2967824



14 mm PLC-HC basic terminal blocks with screw connection method, input voltage 230 V AC/DC (without relay or optocoupler)

Commercial data	
EAN	4017918174231
Pack	10 pcs.
Customs tariff	85364190
Weight/Piece	0.0598 KG

### Product notes

WEEE/RoHS-compliant since: 01/16/2007



<http://www.download.phoenixcontact.com>  
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

## Technical data

Input data	
Nominal input voltage $U_N$	230 V AC/DC
Status display	LED

Output data	
Compatible components	Miniature relay, REL-MR-110DC/21HC

---

**Connection data**

Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Type of connection	Screw connection
Stripping length	8 mm
Screw thread	M3

**General data**

Length	80 mm
Width	14 mm
Height	94 mm
Color	green
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Operating mode	100% operating factor
Inflammability class acc. to UL 94	V0
Standards/regulations	IEC 60255/DIN VDE 0435 (in relevant parts) DIN EN 50178/DIN VDE 0160 (in relevant parts) EN 60730/DIN VDE 0631
Mounting position	Any
Assembly instructions	In rows with zero spacing

**Certificates / Approvals**

Certification

CUL, CUL Listed, GL, GOST, UL, UL Listed

---

**Address**

PHOENIX CONTACT UAB  
Svitrigailos Str. 11b  
03228 Vilnius, LITHUANIA  
Phone +370 5 2106321  
Fax +370 5 2106324  
<http://www.phoenixcontact.lt>



© 2009 Phoenix Contact  
Technical modifications reserved;