

Datasheet

RS Pro MAWI Series, 5 Pole Right Angle Din Connector Plug, 4A, 34 V ac/dc IP30

RS Stock No: 776-606



Product Details

RS Pro 5-pole right angle DIN connector plug has a current rating of 4 A and voltage rating of 34 V ac/dc. It is IP30 rated. Plastic screened DIN connectors suitable for a wide variety of applications, will mate with the plastic chassis mount sockets.

Features and Benefits

- Cable acceptance 5.5 mm maximum
- Tin plated contacts with UL94V-2 rated housings
- IP30 rated

Specifications:

Body Orientation	Right Angle
Connector Size	Standard
Contact Material	Brass
Contact Plating	Tin
Current Rating	4 A
DIN Number	DIN 41524
Gender	Male
Housing Material	PE
IP Rating	IP30
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-20°C
Mounting Type	Cable
Number of Contacts	5
Shielded/Unshielded	Shielded
Termination Method	Solder
Voltage Rating	34 V ac/dc
Contact Resistance	≤4 mΩ