



Hakko FR-300 Portable desoldering Gun

Features:

1. Temperature sensing with quick recuperation
2. Barrel of moderate size and weight
3. One-touch, quick and convenient replacement of Nozzle , ad hoc special extractor
4. Easy replacement of fliter tube in a single click

Standard:

1. Power: 95W
2. Temperature range: 350~500
3. Impedance between nozzle and ground: below 2
4. Potential difference between nozzle and ground: below 2mV
5. Vacuum launch: Diaphragm
6. Vacuum pressure: 81kPa (610mmHg)
7. Suction flow: 11L/min
8. Wire length: 1.6m
9. Outside size: 210(W) x 192(H) x 47(D)
10. Standard nozzle: 1.0mm (Type: N50-04)