

Datasheet

RS Pro IP66, IP67 Red Flush Mount 3P+N+E Heavy Duty Power Connector Socket, Rated At 16A, 346 to 415 V

RS Stock No: **795-9886**



Product Details

RS Pro IP66, IP67 red flush mount 3P+N+E heavy duty power connector socket has a voltage rating of 346 to 415 V and current rating of 16 A. This straight, female power connector socket features robust design with plastic construction for durability. It is well suited to industrial purposes.

Features and Benefits

- A range of angled panel mount sockets offered in a variety of colours and contact layouts in 16 and 32 A versions
- This splash proof, female socket is well suited to industrial purposes
- Made from engineering plastic

Specifications:

Body Orientation	Straight
Colour	Red
Current Rating	16 A
Gender	Female
IP Rating	IP66, IP67, IP69
Mounting Type	Flush Mount
Plug/Socket	Socket
Pole Format	3P+N+E
Termination Method	Screw
Voltage Rating	346 to 415 V
Earthing Position	6 h
Operating Frequency	50/60 Hz
Standards Met	CE, IMQ - ENEC 03, CCC, EN 60309-1, 2, 1/A1, 2/A1