

5

4

3

2


1

SPECIFICATION

Performance level	PL2
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB

PCB Layout, Component side, thickness 1.6 mm





				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, female, angled, 9 Poles, solder pins, board-locks and clinch nuts	Mo?Mstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
36283	12/01/12	SD	Insp.	12/01/12	JB			
33231	07/10/05	JMDR	Stand.					
32134	16/08/04	TR	HARTING EURL F-95972 Paris				TB 0964114723x	Blatt/ Page 1 / 4
31058	8-JUL-02	CV						
Mod.	Dat.	Name						
						Sub.		

D

C

B

A



09641147233	M3
09641147232	UNC 4-40
Part number	Nut thread