







1:1



Steckgesicht n.
Contact face acc.
IEC 61076-2-101



Leiterquerschnitt: 0,34-0,5mm²/ AWG 22-20
conductor cross-section: 0,34-0,5mm²/ AWG 22-20

 ALL Dimensions in mm Original Size DIN A 4			Techn. Character.				Nicht tolerierte Masse/ Free size tolerances	
				Dat.	Name	Massstab/ Scale 2:1 1:1	Rundsteckverbinder M12-L/ Circular connector M12-L 5polig Buchse A-kodiert 5poles female A-coded	
			Detail.	19.04.06	DY			
			Insp.		SP			
			Stand.					
412800	19.03.07	DY	HARTING Electric GmbH & Co. KG D-32339 Espelkamp				TB 21 03 272 2505	
411702								
Mod.	Dat.	Name					Sub.	