

Within Series Adaptor 31_BNC-75-0-1/133_N

Description

Adaptor jack/jack
BNC jack (female) / BNC jack (female)

Interface standard
Series BNC - Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120



Technical Data

Electrical Data

Impedance 75 Ω
Interface frequency max. 1 GHz

Mechanical Data

Number of matings 500
Weight 0.0121 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EC (RoHS) compliant

Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00013802

Ordering Information

Single package 31_BNC-75-0-1/133_NE