


Datasheet

N type open end cable assembly

RS Stock number 794-2875



Dimensions: (mm)



Specification

PRODUCT MATERIAL

- 1.N B/H JACK CRIMP TYPE FOR $\varnothing 1.37\text{mm}$ CABLE NUT x 1,WASHER x 1
- 2.1.37mm CABLE TIN PLATED COLOR:BLACK
- 3.HEAT SHRINK TUBE F32 $\square 2.5\text{mm}$ L=15.0mm COLOR:BLACK

ELECTRICAL PERFORMANCE:

- 1.IMPEDANCE:50 OHMS
- 2.FREQUENCY RANGE:DC~3GHz
- 3.WORKING VOLTAGE:250Vrms MAXIMUM
- 4.DIELECTRIC WITHSTANDING VOLTAGE:750Vrms min.