


Product Datasheet

SCRD TWISTED PAIR-9 50M

RS Article No: 812-4703



Cross Section:



Cable Marking: 9PR 22AWG SCRD TWIST 001M..50M

Construction:

Conductor: Tinned Copper

AWG: 22

Structure: 7/0.254

Conductor Dia. Nom. (mm): 0.76

Insulation: PP

Average Thickness(mm): 0.25

Insulation Dia. Nom. (± 0.20 mm): 1.25

Twisted: 2C

PET(Each Pair): YES

Drain (Each Pair): Tinned Copper

Structure: 7/0.25

AL-Mylar(Each Pair AL Facing in)

PET(Each Pair): YES

Assembly: 9P+PVC(Filler)

PET(Overall): YES

Sheath : PVC

Average Thickness(mm): 0.95

Min point Thickness(mm): 0.80

Outer Dia. Nom. (± 1.0 mm): 11.0

Colour:

**Insulation colours: Black-Red, Black-White, Black-Green, Black-Blue, Black-Yellow,
Black-Brown, Black-Orange, Red-White, Red-Green**

Jacket color: Grey RAL7037

Electrical Characteristics:

Max. Conductor DC Resistance @20°C (ohms/km): 54.0