

Datasheet

RS Pro Straight Subminiature 50Ω SSMB Connector, Plug, Clamp Termination RG405

RS Stock No: **738-5825**



Product Details

RS Pro subminiature SSMB connector plug is designed for 50 Ω impedance applications. This straight connector jack is suitable for use at high operational frequencies. It offers clamp termination and is compatible with RG405 cables.

Features and Benefits

- Nominal impedance 50Ω
- Gold plated copper contacts
- Suitable for use with RG405 cable

**Specifications:**

Body Orientation	Straight
Body Plating	Gold
Cable Type	RG405
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Operating Frequency	4 GHz
Size	Subminiature
Termination Method	Clamp
Dimensions	10.8 x 4.8 mm
Operating Temperature Range	-65 to +165°C