



3M Worldwide : United States : Utilities & Telecommunication

 Search This Product
Catalog

[Product Catalog for Access Network Solutions > Fiber Connectors, Splices, Couplings and Cable Assemblies > Fiber Connectors and Couplings > ST Connectors and Couplings > Epoxy ST Connectors >](#)

 [Printer-friendly format](#) **6105-B Connector ST Compatible MM Black Boot**



The Epoxy ST* Connector is bayonet style for quick interconnect and high repeatability.

[\[click to enlarge\]](#)

3M Id : 80-6107-4705-9

GTIN(UPC/EAN) : 0 00 54007 91144 9

Additional Information

Learn More . . .

[Packaging Data](#)

[Epoxy Bayonet ST Connectors Features and Benefits - Features and Benefits- \(JPG\)](#)

[Fiber Optic ST and FC Connectors - Instructions/Manual \(PDF 662.8 K\)](#)

[SC_FC_ST Hot Melt Fiber Optic Connectors - Instructions/Manual \(PDF 534.1 K\)](#)

[ST Connector - Illustration/Line Art](#)

[ST Connector - Illustration/Line Art](#)

[ST Connector Lineart - Illustration/Line Art- \(TIFF\)](#)

[ST Connectors Lineart - Illustration/Line Art- \(TIFF\)](#)

[ST FC Epoxy Instructions - Instructions/Manual \(PDF 657.3 K\)](#)

[ST* Connectors and Accessories - Bulletin \(PDF 515.6 K\)](#)

Please Note:

Adobe® Acrobat® Reader is required to view PDF documents.



Characteristics

Boot Material	Estane
Flame Retardant	UL-94 V-O

Operating Temperature Range	-40 to 80 Degree Celsius
Primary Trademark Name	3M
Storage Temperature	-40 to 85 Degree Celsius