

Screw termination block - CT-TERMIBLOCK 10 DA - 0441711

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Screw termination block with disconnect contacts for accommodating protective plugs CT and CTM. Use in MCR and telecommunications systems. Design: 10 double wires

Why buy this product

- For COMTRAB protective plugs
- Automatically closing feed-through/disconnect contacts
- Ground terminal blocks on both sides with plug-in connection for the protective plugs used
- Mounting on DIN rails according to EN 60715



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 002213
Weight per Piece (excluding packing)	168.5 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Height	43 mm
Width	118 mm
Depth	40.9 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
Degree of protection	IP20

General

Housing material	PA
Inflammability class according to UL 94	V2
Color	black

Screw termination block - CT-TERMIBLOCK 10 DA - 0441711

Technical data

General

Standards for air and creepage distances	IEC 60664-1
Surge voltage category	III
Pollution degree	3
Mounting type	NS 32/NS 35
Type	LSA-PLUS module

Protective circuit

Maximum continuous voltage U_C (wire-wire)	240 V AC
Maximum continuous voltage U_C (wire-ground)	250 V AC
Operating effective current I_C at U_C	5 A

Connection data

Connection method	Screw terminal blocks
Connection type IN	Screw terminal blocks
Connection type OUT	Screw terminal blocks
Screw thread	M3
Tightening torque	0.5 Nm
Stripping length	7 mm
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	14

Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000371
ETIM 5.0	EC000371

Screw termination block - CT-TERMIBLOCK 10 DA - 0441711

Classifications

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

Approvals

Approvals


Approvals

GOST / UL Listed

Ex Approvals

Approvals submitted

Approval details



Drawings

Screw termination block - CT-TERMIBLOCK 10 DA - 0441711

Dimensioned drawing

