

General Information

Extended Product Type:	BJM62
Product ID:	1SNA173226R2700
EAN:	3472591732269
Catalog Description:	BJM62-10 Jumper Bars
Long Description:	BJM62 - Jumper Bars - 10 poles - - 6mm Spacing

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks Accessories » Jumper Bars

Ordering

EAN:	3472591732269
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	10.00 g
----------------------------	---------

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	125 mm
Package Level 1 Height:	5 mm
Package Level 1 Length:	170 mm
Package Level 1 Gross Weight:	0,1 kg
Package Level 1 EAN:	3472591732269
Package Level 2 Units:	800 piece
Package Level 2 Width:	175 mm
Package Level 2 Height:	130 mm
Package Level 2 Length:	227 mm
Package Level 3 Units:	144000 piece

Additional Information

Function:	Jumper Bars
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	BJM
Product Name:	Jumper Bar
Rated Current (I_n):	Main Circuit 32 A
Spacing:	6 mm
Sub-Function:	Assembled jumper bar

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225001C1009

GOST Certificate: 1SND161005A1104

Classifications

ETIM 4.0: EC000489 - Cross-connector for terminal block

ETIM 5.0: EC000489 - Cross-connector for terminal block

Object Classification Code: X
